


Required total space for emitter change: 3320mm



Mounting position vertical or horizontal possible!

Attention!
For horizontal mounting do not arrange the UV-Sensor on the highest or lowest Point!

Display window

230

Minimum distance for UV-Sensor removal

610

Flange DN250
PN16 1.4301

Connection sampling faucet
1/4"

Drainage faucet
1/2"

1245

1745

211

UV-Disinfection System VISADES T2500L-300

Technical changes and errors reserved!

VISADES
UV-TECHNOLOGY

Dimension sheet chamber

UV-System T2500L-300

5023 Salzburg Tel. 0662 871224 0
Mauermannstraße 2 Fax 0662 871224 10
eMail: office@visades.com